

# Eaton CHP60B225X9

Catalog Number: CHP60B225X9

Eaton CH main breaker loadcenters, PON, Main breaker, 225 A, X9, Copper, X9, NEMA 1, Metallic, 25 kAIC, CSR, 120, 60, Three-wire, Single-phase, #2 AWG-300 kcmil, 120/240 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CHP60B225X9
<b>UPC</b>	<b>Product Length/Depth</b>
786679189672	45 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
31 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Purchase Size X9 Cover Separately

## Product specifications

### Special features

PON

### Type

Main breaker

### Amperage Rating

225 A

### Bus material

Copper

### Cover

X9

### Main circuit breaker

CSR

### Number of circuits

120

### Number of spaces

60

### Phase

Single-phase

### Wire size

#2 AWG-300 kcmil

### Voltage rating

120/240 V

### Box size

X9

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP60B225X9](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)