

# Eaton CHQ150

Catalog Number: CHQ150

3/4" Thermal magnetic circuit breakers, Type CHQ 3/4-Inch classified replacement breaker clamshell pack, Ground fault, 50 A, 10 kAIC, Single-pole, 120/240V, CHQ, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, Q30, CHQ, Type CH Loadcenters

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Classified 3/4" thermal magnetic circuit breaker	CHQ150
	<b>UPC</b>
	782113010885
<b>Product Length/Depth</b>	<b>Product Height</b>
2.5 in	3 in
<b>Product Width</b>	<b>Product Weight</b>
0.8 in	0.3 lb
<b>Warranty</b>	<b>Certifications</b>
Limited lifetime residential, 1 year commercial	UL 489
	<b>Catalog Notes</b>
	Replacement for Square D Type QO Breakers. Requires one 3/4-inch (19.1 mm) space.

## defaultTaxonomyAttributeLabel

### Type

Type CHQ 3/4-Inch classified replacement breaker clamshell pack

### Special features

Ground fault

### Amperage Rating

50 A

### Voltage rating

120/240 V

### Circuit breaker type

CH

### Used with

Type CH Loadcenters

### Interrupt rating

10 kAIC

### Main circuit breaker

CHQ

### Wire size

(2) #14-10 AWG Cu/Al

(1) #14-8 AWG

### Number of poles

Single-pole

### Quantity

30

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

[Standard circuit breaker catalog numbers - 5651B63SH09](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHQ150](#)