

Specifications



Photo is representative



Eaton CHR8N8N5NS

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Circuits: 4, 1, Weather-resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: NEMA 6-20R2, Ringless

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHR8N8N5NS
UPC	786685948461
PRODUCT LENGTH/DEPTH	31 in
PRODUCT HEIGHT	8 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	24 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Metered-ringless
	IA : Alliant (IP&L and WP&L) WI : Alliant (IP&L and WP&L) FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power,
UTILITY APPROVALS	