

# Eaton CHR8N8N5NSU

Catalog Number: CHR8N8N5NSU

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Circuits: 4, 1, Weather resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: NEMA 6-20R2, Ringless

## General specifications



Photo is representative

### Product Name

Eaton pedestal mount metered

### UPC

786685948430

### Product Height

7.125 in

### Product Weight

30 lb

### Catalog Number

CHR8N8N5NSU

### Product Length/Depth

30.875 in

### Product Width

9.75 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Metered-ringless

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Non-ground fault

### Receptacle center

5-20R2GFI WR

### Receptacle left

5-20R2GFI WR

### Receptacle right

6-20R2

### Feed type

BOTTOM

### Number of sockets

1

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHR8N8N5NSU](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHR8N8N5NSU

Catalog Number: CHR8N8N5NSU

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Circuits: 4, 1, Weather resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: NEMA 6-20R2, Ringless

## General specifications



Photo is representative

### Product Name

Eaton pedestal mount metered

### UPC

786685948430

### Product Height

7.125 in

### Product Weight

30 lb

### Catalog Number

CHR8N8N5NSU

### Product Length/Depth

30.875 in

### Product Width

9.75 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Metered-ringless

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Non-ground fault

### Receptacle center

5-20R2GFI WR

### Receptacle left

5-20R2GFI WR

### Receptacle right

6-20R2

### Feed type

BOTTOM

### Number of sockets

1

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHR8N8N5NSU](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)