

Specifications



Photo is representative



Eaton CHR8N8N5NSU

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Circuits: 4, 1, Weather resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: NEMA 6-20R2, Ringless

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHR8N8N5NSU
UPC	786685948430
PRODUCT LENGTH/DEPTH	30.875 in
PRODUCT HEIGHT	7.125 in
PRODUCT WIDTH	9.75 in
PRODUCT WEIGHT	30 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications	
TYPE	Metered-ringless
CIRCUIT BREAKER POSITION 1	Non-ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	Non-ground fault
RECEPTACLE CENTER	5-20R2GFI WR
RECEPTACLE LEFT	5-20R2GFI WR
RECEPTACLE RIGHT	6-20R2
FEED TYPE	BOTTOM
NUMBER OF SOCKETS	1

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHR8N8N5NSU
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

