

# Eaton CHR8N8NSU

Catalog Number: CHR8N8NSU

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Bottom, Surface, Circuits: 4, Weather-resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: None, Ringless

## General specifications



Photo is representative

### Product Name

Eaton pedestal mount metered

### Catalog Number

CHR8N8NSU

### UPC

786685404202

### Product Length/Depth

7.25 in

### Product Height

31 in

### Product Width

10 in

### Product Weight

30 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL 231

UL Listed file E163588

## Product specifications

### Special features

Water resistant left/center receptacle

### Type

Metered-ringless

### Circuit breaker position 1

Ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

None

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA 5-20R2GFI

### Receptacle right

None

### Feed type

Bottom

### Mounting

Surface

### Number of circuits

4

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHR8N8NSU](#)