



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## SPD Type 2 CHSP Service Entrance Surge Protection

**CHSPT2SURGE**

**UPC:**786685971285

### Dimensions:

- **Height:** 2 IN
- **Length:** 7.5 IN
- **Width:** 5 IN

**Weight:**.85 LB

**Notes:**5kA nominal discharge current. Has 36kA one time surge current rating.

### Warranties:

- Limited lifetime

### Specifications:

- **Frequency Rating:** 60 Hz
- **Nominal Discharge Current:** 5000 KA
- **Operating Voltage:** 150V L-N, 300V L-L
- **Protection:** 700V L-N, 1200V L-L, 900V N-G, 700V L-G
- **Short Circuit Rating:** 22000 KA
- **Voltage Rating:** 120/240V
- **Enclosure:** NEMA 4
- **Phase:** Single-phase
- **Surge Current:** 36 kA

### Supporting documents:

- [Eaton Specification Sheet - CHSPT2SURGE](#)

**Certifications:** No Data

**Product compliance:** No Data

