



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHU1NSFEMA Unmetered Surface Mount 14-50R W/50A BRKR

Eaton Corp

Catalog Number	CHU1NSFEMA
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Unmetered, 50A, None, None, Non-Ground Fault, None, None, CH, Top, Surface, Circuits: 4, Nema 14-50R, None, None, 4, 0, 0, 125/250V, None, None
Weight per unit	8.3 (lbs/each)
Product Category	Unmetered Power Outlet Panels

### Features

dimensions	4.3000 IN X 9.5000 IN X 17.1000 IN
------------	------------------------------------

### Dimensions and Weight

Depth	4.3000
Height	17.1000
Width	9.5000

### Descriptions

Description	UNMETERED SURFACE MOUNT 14-50R W/50A BRKR
extra long description	ETN CHU1NSFEMA Unmtrd Surf Mount 14
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount unmetered, Unmetered, 50A, None, None, Non-ground fault, None, None, CH, Top, Surface, Circuits: 4, NEMA 14-50R, None, None, 4, 0, 0, 125/250V, None, None
Product Type	Unmtrd Surf Mount 14-50R W/50A BRKR

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116910205
Manufacturers Part Number	CHU1NSFEMA
UPC	782116910205

### Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered

### Packaging

Carton	1
Weight Per each	8.25



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting standard	SURFACE UL 231,UL Listed file E163588