

# Eaton CHU7N7NS

Catalog Number: CHU7N7NS

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton pedestal mount unmetered	CHU7N7NS
<b>UPC</b>	<b>Product Length/Depth</b>
782114203774	6.8 in
<b>Product Height</b>	<b>Product Width</b>
39.9 in	9.5 in
<b>Product Weight</b>	<b>Warranty</b>
16 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Certifications

UL 231  
UL Listed file E163588

## Product specifications

### Type

Unmetered

### Circuit breaker position 1

Ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

None

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA 5-20R2GFI

### Receptacle right

None

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHU7N7NS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)