



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CK221RP 2 PB Chime Kit

Abb Installation Products, Inc

| | |
|------------------|------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | CK221RP |
| Manufacturer | Abb Installation Products, Inc |
| Description | Wired White Contractor Door Chime Kit. Kit Includes Chime, 16V, 10VA Transformer and Two Unlighted White Push Buttons. |
| Weight per unit | 1.8 (lbs/each) |
| Product Category | Builders Products |

Features

| | |
|-----------------|----------|
| Button Type | Push |
| Inside Diameter | 4,000 ft |
| Material | 4,000 ft |
| Voltage Rating | 16 V |

Material, Color, and Finish

| | |
|-------|-------|
| Color | White |
|-------|-------|

Descriptions

| | |
|------------------------|------------------------------------------------------------------------------------------------------------------------|
| Description | 2 PB CHIME KIT |
| extra long description | CL CK221RP CHIME KIT W/TWO BUTTONS |
| Long Description | Wired white contractor door chime kit. Kit includes chime, 16V, 10VA transformer and two unlighted white push buttons. |
| Product Type | Chime Kit W/Two Buttons |
| Special Features | Sounds two notes for front door and one note for back doo |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Carlton |
| GTIN | 00034481043249 |
| Manufacturers Part Number | CK221RP |
| UPC | 034481043249 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------|
| Category Description | PUSHBUTTONS & CHIMES |
| Type | Wired Door Chime Kits |

Availability

| | |
|---------------------|----------|
| Manufacturer Status | Inactive |
| Status | Inactive |

Packaging

| | |
|-----------------|------|
| Carton | 9 |
| Weight Per each | 1.75 |

Uses, Certifications, and Standards

| | |
|-------------|----------|
| Application | 4,000 ft |
|-------------|----------|