

# Eaton CL120

Catalog Number: CL120

Eaton Classified 3/4" thermal magnetic circuit breaker, Type CL 1-Inch classified replacement breaker, 20 A, 10 kAIC, Single-pole, 120/240V, CL, #14-4 AWG Cu/Al, CL, Type CH Loadcenters

## General specifications



### Product Name

Eaton Classified 3/4" thermal magnetic circuit breaker

### Catalog Number

CL120

### UPC

786676011556

### Product Length/Depth

3 in

### Product Height

3 in

### Product Width

1 in

### Product Weight

0.3 lb

### Warranty

Limited lifetime residential, 1 year commercial

### Certifications

UL 489

### Catalog Notes

Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires 1-inch (25.4 mm) space.

**Type**

Type CL 1-Inch classified replacement breaker

**Amperage Rating**

20 A

**Voltage rating**

120/240 V

**Circuit breaker type**

CH

**Used with**

Type CH Loadcenters

**Interrupt rating**

10 kAIC

**Main circuit breaker**

CL

**Wire size**

#14-4 AWG Cu/Al

**Number of poles**

Single-pole

**Brochures**

[Loadcenters and Circuit Breakers](#)

[Standard circuit breaker catalog numbers - 5651B63SH09](#)

**Catalogs**

[Eaton's Volume 1—Residential and Light Commercial](#)

**Specifications and datasheets**

[Eaton Specification Sheet - CL120](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)