



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21415 North 15th Lane Suite 116
85027-0000, AZ Phoenix
Phone: 480-681-0668
Fax: 480-681-0669



CL140 Type CL BRKR 40A/1POLE 120/240V 10K-Classified 1" *Eaton Corp*

Catalog Number	CL140
Manufacturer	Eaton Corp
Description	Eaton Classified 1" Thermal Magnetic Circuit Breaker, Type CL 1-Inch Classified Replacement Breaker, 40 A, 10 Kaic, Single-Pole, 120/240V, CL, #14-4 Awg Cu/Al, CL, Type CH Loadcenters
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

amps	40
dimensions	3.0000 IN X 1.0000 IN X 3.0000 IN
interrupt rating	10
pole	Single
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE CL BRKR 40A/1POLE 120/240V 10K-CLASSIFIED 1"
extra long description	ETN CL140 CL bkr 40A/1Pole 120/240V
Features	Eaton UL classified replacement circuit breakers are available in both 3/4-inch Type CHQ and 1-inch Type CL, single- and two-pole configurations. These breakers are classified as direct replacements by Underwriters Laboratories. In addition to a UL listing, they also come with a 15-year warranty.
Long Description	Eaton Classified 1" thermal magnetic circuit breaker, Type CL 1-Inch classified replacement breaker, 40 A, 10 kAIC, single-pole, 120/240V, CL, #14-4 AWG Cu/Al, CL, Type CH loadcenters
Product Type	CL BKR 40A/1POLE 120/240V 10K

Manufacturer Information

Brand	Eaton
GTIN	00786676011594
Manufacturers Part Number	CL140
UPC	786676011594

Taxonomies, Classifications, and Categories

Category Description	CLASSIFIED BREAKERS
Type	1" Thermal magnetic circuit breakers

Packaging

Carton	10
Package	50
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21415 North 15th Lane Suite 116
85027-0000, AZ Phoenix
Phone: 480-681-0668
Fax: 480-681-0669

Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489