

# Eaton CL140

Catalog Number: CL140

Eaton Classified 3/4" thermal magnetic circuit breaker, Type CL 1-Inch classified replacement breaker, 40 A, 10 kAIC, Single-pole, 120/240V, CL, #14-4 AWG Cu/Al, CL, Type CH Loadcenters

## General specifications



### Product Name

Eaton Classified 3/4" thermal magnetic circuit breaker

### Catalog Number

CL140

### UPC

786676011594

### Product Length/Depth

3 in

### Product Height

3 in

### Product Width

1 in

### Product Weight

0.3 lb

### Warranty

Limited lifetime residential, 1 year commercial

### Certifications

UL 489

### Catalog Notes

Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires 1-inch (25.4 mm) space.

## defaultTaxonomyAttributeLabel

### Type

Type CL 1-Inch classified replacement breaker

### Amperage Rating

40 A

### Voltage rating

120/240 V

### Circuit breaker type

CH

### Used with

Type CH Loadcenters

### Interrupt rating

10 kAIC

### Main circuit breaker

CL

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Single-pole

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

[Standard circuit breaker catalog numbers - 5651B63SH09](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - CL140](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)