



CPR22 3/4" Rigid Coupling Threadless

Crouse-Hinds

Catalog Number	CPR22
Manufacturer	Crouse-Hinds
Description	Threadless Coupling, 3/4 In Trade Size, CPR Model, Straight, 38 LB/100
Weight per unit	0.3200 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

dimensions	1.8800 IN X 1.6300 IN X 1.6300 IN
Material	Malleable Iron

Descriptions

Description	3/4" RIGID COUPLING THREADLESS
extra long description	MIDWEST CPR22 3/4 RGD CMP CPL
Features	Crouse-Hinds series rigid/IMC connectors, couplings and combination couplings are used to join used to join rigid/IMC conduit to a box or enclosure, or to couple two ends of conduit together. Our rigid/IMC connectors and couplings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in a variety of materials to suit customer preferences, including malleable iron, steel, zinc die cast, aluminum, stainless steel and hot dip galvanized mallea

Manufacturer Information

Brand	Eaton
GTIN	00784564122223
UPC	784564122223

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression coupling

Packaging

Carton	1
Package	20
Weight Per each	0.32

Uses, Certifications, and Standards

standard	UL 514B, CUL
----------	--------------