



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 North Jackson Suite E  
78501-0000, TX McAllen  
Phone: 956-331-2410  
Fax: 956-331-2411



## CPR4 1-1/4" Rigid Connector Threadless

*Crouse-Hinds*

Catalog Number	CPR4
Manufacturer	Crouse-Hinds
Description	Connector, 1-1/4 In Trade Size, CPR Model, Straight, Non-Insulated, 64 LB/100
Weight per unit	0.2200 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

dimensions	2.0000 IN X 2.3800 IN X 2.3800 IN
Material	Malleable Iron

### Dimensions and Weight

Size	1-1/4 in
------	----------

### Descriptions

Construction	Concrete Tight
Description	1-1/4" RIGID CONNECTOR THREADLESS
extra long description	MIDWEST CPR4 1 1/4 RGD CMP CONN
Features	Crouse-Hinds series rigid/IMC connectors, couplings and combination couplings are used to join used to join rigid/IMC conduit to a box or enclosure, or to couple two ends of conduit together. Our rigid/IMC connectors and couplings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in a variety of materials to suit customer preferences, including malleable iron, steel, zinc die cast, aluminum, stainless steel and hot dip galvanized mallea

### Manufacturer Information

Brand	Eaton
GTIN	00784564122049
UPC	784564122049

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression Connector

### Packaging

Carton	10
Weight Per each	0.22

### Uses, Certifications, and Standards

standard	UL 514B, CUL
----------	--------------