



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS320I Switch, Spec, 3W, 20A 120/277V, Iv *Hubbell Wiring Devices*

Catalog Number	CS320I
Manufacturer	Hubbell Wiring Devices
Description	Toggle Switch, 1 Pole, 3 Ways, 20 A, 120 to 277 V Ac, SPDT Contact Configuration, Thermoset (Body);Nylon (Toggle) Material, Steel Contact Material, Ivory, Back and Side Wired Connection, Screw Mount, Zinc Plated (Bridge), 1.49 In (L) X 1 In (W) X 4.18 In (H), -40 °C Operating Temperature, +75 °C Operating Temperature, 0.15 LB
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	SPDT
amperage rating	20
connection	Side Wired Only
Contact Rating	Per UL 20
insulation	False
operating cycles	50,000
pallet quantity	5000
Poles	Single Pole
Switch Type	Toggle
Wattage	5540;5540.0000

Dimensions and Weight

Size	4.18 in x 1.49 in x 1.83 in
------	-----------------------------

Descriptions

Description	SWITCH, SPEC, 3W, 20A 120/277V, IV
extra long description	HWDK CS320I SWITCH, SPEC, 3W, 20A 1

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585902159
series	General Purpose
UPC	783585902159

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	TOGGLE

Packaging

Carton	10
Weight Per each	0.15



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed