

# Specifications



## Eaton CS8369

Eaton locking receptacle, #10-6 AWG, 50A, Industrial, 250V, Back wiring, Black, Single, Non-NEMA, Three-pole, Four-wire, Steel, California standard

### General specifications

|                                 |                                                               |
|---------------------------------|---------------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Arrow Hart<br>California standard locking<br>receptacle |
| <b>CATALOG NUMBER</b>           | CS8369                                                        |
| <b>UPC</b>                      | 040893676715                                                  |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 6.25 in                                                       |
| <b>PRODUCT HEIGHT</b>           | 3.25 in                                                       |
| <b>PRODUCT WIDTH</b>            | 3 in                                                          |
| <b>PRODUCT WEIGHT</b>           | 0.88 lb                                                       |
| <b>COMPLIANCES</b>              | RoHS Compliant                                                |
| <b>CERTIFICATIONS</b>           | UL Listed<br>CSA certified<br>cULus Listed                    |
| <b>PRODUCT TYPE</b>             | California standard                                           |

## Product specifications

|                              |                               |
|------------------------------|-------------------------------|
| <b>SPECIAL FEATURES</b>      | Locking plug                  |
| <b>TYPE</b>                  | Locking receptacle            |
| <b>AMPERAGE RATING</b>       | 50 A                          |
| <b>VOLTAGE RATING</b>        | 3Ø 250 V                      |
| <b>CONTACT MATERIAL</b>      | Zinc plated brass             |
| <b>APPLICATION</b>           | Industrial                    |
| <b>DEVICE GRADE</b>          | Extra heavy duty              |
| <b>WIRING METHOD</b>         | Back                          |
| <b>NUMBER OF WIRES</b>       | 4<br>Grounding                |
| <b>NUMBER OF POLES</b>       | Three-pole                    |
| <b>COLOR</b>                 | Black                         |
| <b>MATERIAL</b>              | Steel                         |
| <b>OPERATING TEMPERATURE</b> | -40 to 105 °C (-40 to 221 °F) |
| <b>STANDARD</b>              | California standard           |
| <b>ALLOWABLE WIRE SIZE</b>   | #10-6 AWG                     |
| <b>NEMA CONFIGURATION</b>    | Non-NEMA                      |
| <b>TORQUE RATING</b>         | 45 lbf-inch                   |
| <b>DESIGN TYPE</b>           | Single receptacle             |
| <b>FACE/BODY MATERIAL</b>    | Glass filled nylon            |
| <b>RECEPTACLE TYPE</b>       | Locking                       |

## Resources

### MULTIMEDIA

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

### SPECIFICATIONS AND DATASHEETS

[Hart lock industrial grade 50A locking devices spec sheet](#)

[Eaton Specification Sheet - CS8369](#)

[Industrial grade 50A locking devices spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

