

Specifications

Eaton CSB115V

Eaton commercial grade toggle switch, #14-10 AWG, 15A, Commercial, Flush, 120/277V, Back and side, Screw, Ivory, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC

General specifications

PRODUCT NAME	Eaton commercial grade toggle switch
CATALOG NUMBER	CSB115V
UPC	032664558894
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.2 in
PRODUCT WIDTH	0.902 in
PRODUCT WEIGHT	0.2 lb
CERTIFICATIONS	cULus Listed NOM Federal Specification Classification 6241 05
PRODUCT TYPE	Commercial grade toggle switch



Powering Business Worldwide

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	15A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
APPLICATION	Commercial
WIRING METHOD	Back and side
SWITCH TYPE	Single-pole
MOUNTING METHOD	Flush
CONNECTOR TYPE	Screw
LOAD TYPE	MLV LED ELV Fan HAL INC CFL Motor Control FLR
MATERIAL	PVC
ALLOWABLE WIRE SIZE	#14-10 AWG
TERMINAL ENCLOSURE MATERIAL	Brass
TERMINALS	0.031 in
COLOR	Ivory

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CSB115V
	Commercial specification grade switches spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton CSB115V

Eaton commercial grade toggle switch, #14-10 AWG, 15A, Commercial, Flush, 120/277V, Back and side, Screw, Ivory, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC

General specifications

PRODUCT NAME	Eaton commercial grade toggle switch
CATALOG NUMBER	CSB115V
UPC	032664558894
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.2 in
PRODUCT WIDTH	0.902 in
PRODUCT WEIGHT	0.2 lb
CERTIFICATIONS	cULus Listed NOM Federal Specification Classification 6241 05
PRODUCT TYPE	Commercial grade toggle switch



Powering Business Worldwide

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	15A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
APPLICATION	Commercial
WIRING METHOD	Back and side
SWITCH TYPE	Single-pole
MOUNTING METHOD	Flush
CONNECTOR TYPE	Screw
LOAD TYPE	MLV LED ELV Fan HAL INC CFL Motor Control FLR
MATERIAL	PVC
ALLOWABLE WIRE SIZE	#14-10 AWG
TERMINAL ENCLOSURE MATERIAL	Brass
TERMINALS	0.031 in
COLOR	Ivory

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CSB115V
	Commercial specification grade switches spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

