

Specifications



Eaton CSB320V

Eaton commercial grade toggle switch, #14-10 AWG, 20A, Commercial, Wall, 120/277V, Back and side, Screw, Ivory, Three-Way, Brass, Terminals: 0.031 in

General specifications

PRODUCT NAME	Eaton commercial grade toggle switch
CATALOG NUMBER	CSB320V
UPC	032664559136
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.2 in
PRODUCT WIDTH	0.902 in
PRODUCT WEIGHT	0.125 lb
CERTIFICATIONS	cULus Listed NOM Federal Specification Classification 6241 05
PRODUCT TYPE	Commercial grade toggle switch



Powering Business Worldwide

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	20A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
APPLICATION	Commercial
WIRING METHOD	Back and side
SWITCH TYPE	Three-way
MOUNTING METHOD	Wall
CONNECTOR TYPE	Screw
MATERIAL	PVC
NUMBER OF WAYS	Four-way
ALLOWABLE WIRE SIZE	#14-10 AWG
TERMINAL ENCLOSURE MATERIAL	Brass
TERMINALS	0.031 in
COLOR	Ivory

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CSB320V](#)

[Commercial specification grade switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton CSB320V

Eaton commercial grade toggle switch, #14-10 AWG, 20A, Commercial, Wall, 120/277V, Back and side, Screw, Ivory, Three-Way, Brass, Terminals: 0.031 in

General specifications

PRODUCT NAME	Eaton commercial grade toggle switch
CATALOG NUMBER	CSB320V
UPC	032664559136
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.2 in
PRODUCT WIDTH	0.902 in
PRODUCT WEIGHT	0.125 lb
CERTIFICATIONS	cULus Listed NOM Federal Specification Classification 6241 05
PRODUCT TYPE	Commercial grade toggle switch



Powering Business Worldwide

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	20A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
APPLICATION	Commercial
WIRING METHOD	Back and side
SWITCH TYPE	Three-way
MOUNTING METHOD	Wall
CONNECTOR TYPE	Screw
MATERIAL	PVC
NUMBER OF WAYS	Four-way
ALLOWABLE WIRE SIZE	#14-10 AWG
TERMINAL ENCLOSURE MATERIAL	Brass
TERMINALS	0.031 in
COLOR	Ivory

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CSB320V
	Commercial specification grade switches spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

