



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSD30248WSS 30X24X8 N4X WNDW HC

Hoffman Enclosures, Inc.

Catalog Number	CSD30248WSS
Manufacturer	Hoffman Enclosures, Inc.
Description	Concept Window Door 1/4 Turn Latch Type 4X, 30X24X8, Brushed, Stainless 304
Weight per unit	44.3 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4
Style	Quarter-turn

Dimensions and Weight

Depth	8
Height	30
Size	30.00x24.00x8.00 in
Width	24

Descriptions

Description	30X24X8 N4X WNDW HC
extra long description	NVENT HOF CSD30248WSS 30.00x24.00x8
Features	For indoor or outdoor applications that require corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush quarter-turn latches for secure closure.
Long Description	Concept Window Door 1/4 Turn Latch Type 4X, 30x24X8, Brushed, Stainless 304
Product Type	30.00X24.00X8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510117900
Manufacturers Part Number	CSD30248WSS
UPC	783510117900

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	44.2999

Uses, Certifications, and Standards

Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant