



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2202 East Rusk Street  
75766-0000, TX Jacksonville  
Phone: 903-586-2904  
Fax: 903-586-5271



## CTCL153PHLA Contour 150W Led 3WAY Light Almond Clam *Lutron*

|                  |   |
|------------------|---|
| Catalog Number   | CTCL153PHLA   |
| Manufacturer     | Lutron  |
| Description      | Skylark Contour Led+ Dimmer, Incandescent/Halogen,<br>3-Way/Single-Pole, 150W Led or 600W Inc/Hal, Clamshell<br>Packaging In Light Almond |
| Weight per unit  | 0.2500 (lbs/each)   |
| Product Category | Lighting Dimmers  |

### Features

|                 |               |
|-----------------|---------------|
| actuator        | Rocker/Slide  |
| connection      | Wire Leads    |
| Connection Type | Wire Leads    |
| insulation      | Plastic       |
| Material        | Plastic/Metal |
| media           | Yes           |
| Poles           | 1             |
| Switch Type     | Slide         |
| Voltage Rating  | 120           |
| Wattage         | 600           |

### Material, Color, and Finish

|        |              |
|--------|--------------|
| Color  | Light Almond |
| Finish | Gloss        |

### Dimensions and Weight

|      |                       |
|------|-----------------------|
| Size | 4.69 x 2.94; 119 x 75 |
|------|-----------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2202 East Rusk Street  
75766-0000, TX Jacksonville  
Phone: 903-586-2904  
Fax: 903-586-5271

## Descriptions

|                        |   |
|------------------------|---|
| Description            | CONTOUR 150W LED 3WAY LIGHT ALMOND CLAM   |
| extra long description | LUT CTCL-153PH-LA CONTOUR CFL/LED C   |
| Features               | The Lutron Skylark Contour LED+ dimmer switch includes the most advanced technology for superior dimming for up to 150W of dimmable LED or 600W of Incandescent/Halogen. The Skylark Contour dimmer switch features a smooth, linear slider to dim or brighten the lights while the rocker switch turns lights ON/OFF. Set a favorite preset level with the slider before turning on. The Skylark Contour also features an easy low-end trim adjustment directly on the dimmer which eliminates complicated programming or havi |
| Long Description       | Skylark Contour LED+ Dimmer, Incandescent/Halogen, 3-way/single-pole, 150W LED or 600W inc/hal, clamshell packaging in light almond   |
| Product Type           | Contour CFL/Led Clam Light Almond   |
| Special Features       | Controls 150 W LED/CFL (screw-base) or 600 W incandescent/halogen loads. Rocker switch returns light to light level indicated by slider. Provides reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents.  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Lutron         |
| GTIN                      | 00027557003568 |
| Manufacturers Part Number | CTCL-153PH-LA  |
| UPC                       | 027557003568   |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells      |
| Type                 | Dimmer with on/off switch, 3-way/single-pole, clamshell packaging |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 3    |
| Package         | 48   |
| Weight Per each | 0.25 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2202 East Rusk Street  
75766-0000, TX Jacksonville  
Phone: 903-586-2904  
Fax: 903-586-5271

## Uses, Certifications, and Standards

|                          |                  |
|--------------------------|------------------|
| Application              | Lighting Control |
| Enclosure                | Plastic          |
| environmental conditions | Indoor use only  |
| Mounting                 | WALLBOX          |
| Operating Temperature    | 32 to 104        |
| standard                 | UL, CSA          |