



## CTH44 6SOL-4STR Cop C-Tap

*Nsi Industries*

Catalog Number	CTH44
Manufacturer	Nsi Industries
Description	Heavy Duty Copper C Tap Grounding Connector For 6 to 4 Awg Run - 6-6 Awg Tap Applications: Copper "C" Taps Are Range-Taking Compression Connectors Made From High Conductivity Copper Alloy. Ideal For Making Tap or Parallel Copper Connections From 8 Sol to 4/0 STR Conductors. Provides Consistent Reliability With Heavy Wall Construction That Prevents Relaxation Of The Joint After Installation. Installation Time Is Reduced Because Of Its "C" Shape. UL CU486A, 467 Suitable For Direct Burial.
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Conductor Size	(Run) 6 SOL-4 STR
Material	Copper
Tap Size	4 SOL-4 STR
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Copper
Finish	COPPER

### Dimensions and Weight

Size	L=.625 - W=.437 - H=.812
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

608 Industrial Blvd  
78654-0000, TX Marble Falls  
Phone: 830-693-9910  
Fax: 830-693-0544

## Descriptions

Description	6SOL-4STR COP C-TAP
extra long description	NSI CTH-44 Copper C Tap 6-4 Main 4- Heavy Duty Copper C Tap Grounding Connector for 6 to 4 AWG Run - 6-6 AWG Tap APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial.
Features	
Long Description	Heavy Duty Copper C Tap Grounding Connector for 6 to 4 AWG Run - 6-6 AWG Tap APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial.
Product Type	Copper C Tap 6-4 Main 4-4 Tap
Special Features	(Run) 6 SOL-4 STR - (Tap) 4 SOL-4 STR

## Manufacturer Information

Brand	NSI
GTIN	00662381022158
Manufacturers Part Number	CTH-44
UPC	662381022158

## Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	Copper C Taps

## Packaging

Carton	1
Package	25
Weight Per each	0.04

## Uses, Certifications, and Standards

Application	Terminate-Splice-Tap
environmental conditions	90 C
Temperature Rating	90 C