



CV3 Series

Thermoplastic LED Exit Signs



CV3 thermoplastic exit signs feature an attractive, high impact, UV stable, injection molded enclosure. CV thermoplastic exits offer bright and even LED illumination, low energy consumption, universal chevrons, universal back / ceiling / end mounting, and contractor-friendly quick installation. Emergency version also includes high temperature, long life nickel-cadmium battery. All exit signs meet EPA ENERGYSTAR® requirements.

Standard Features


All Models

- UV-stable thermoplastic housing
- Compact, low-profile design
- Easy to install
- Long-life LED lamps
- Bright, even illumination
- Red and green letters
- Universal single/double face
- White or black finishes
- Push-in wiring connectors
- Universal end/ceiling/wall mount
- Universal snap-in, chevron arrows
- Damp location listed
- 120/277VAC, 60 Hz operation

Emergency Models

- Solid-state charger with low voltage disconnect
- Maintenance-free NiCad battery
- 90 minute emergency operation
- Test switch and AC-On light
- Temperature range: 0°C to 40°C (32°F to 104°F)
- UL 924 Listed
- Available with Spectron® self-diagnostic/self-testing electronics option

Ordering Guide



Options

- I** Spectron self-diagnostic/self-testing electronics ⁽¹⁾
- 2C** 2-circuit operation ⁽²⁾⁽⁶⁾
- FAP** Fire alarm panel interface ⁽³⁾⁽⁵⁾⁽⁶⁾
- FM** Flasher module ⁽¹⁾⁽⁵⁾
- AF** Audible/Flasher module ⁽¹⁾⁽⁵⁾
- DC** Remote DC operation ⁽²⁾⁽⁴⁾⁽⁶⁾
- 24K** 220-240VAC, 60 Hz operation

⁽¹⁾ Available on emergency models only.

⁽²⁾ For use with AC models only.

⁽³⁾ Operates with 24-volt AC or DC fire alarm panels.

⁽⁴⁾ For emergency illumination of sign from remote 6-24 VDC power sources.


⁽⁵⁾ -FAP, -FM, and -AF options may not be specified together.

⁽⁶⁾ -DC option may not be specified with -2C or -FAP.

Accessories

- PMLXB** Pendant mounting kit (black)
- PMLXW** Pendant mounting kit (white)
- WGLX** Wire guard (Wall mount)
- WG-MLT** Wire guard (Wall mount)
- WGLXC** Wire guard (Ceiling mount)
- WGLXE** Wire guard (End mount)

Dimensions



Hubbell Lighting, Inc.



CV3 Series

Thermoplastic LED Exit Signs



CV3 thermoplastic exit signs feature an attractive, high impact, UV stable, injection molded enclosure. CV thermoplastic exits offer bright and even LED illumination, low energy consumption, universal chevrons, universal back / ceiling / end mounting, and contractor-friendly quick installation. Emergency version also includes high temperature, long life nickel-cadmium battery. All exit signs meet EPA ENERGYSTAR® requirements.

Standard Features


All Models

- UV-stable thermoplastic housing
- Compact, low-profile design
- Easy to install
- Long-life LED lamps
- Bright, even illumination
- Red and green letters
- Universal single/double face
- White or black finishes
- Push-in wiring connectors
- Universal end/ceiling/wall mount
- Universal snap-in, chevron arrows
- Damp location listed
- 120/277VAC, 60 Hz operation

Emergency Models

- Solid-state charger with low voltage disconnect
- Maintenance-free NiCad battery
- 90 minute emergency operation
- Test switch and AC-On light
- Temperature range: 0°C to 40°C (32°F to 104°F)
- UL 924 Listed
- Available with Spectron® self-diagnostic/self-testing electronics option

Ordering Guide



Options

- I** Spectron self-diagnostic/self-testing electronics ⁽¹⁾
- 2C** 2-circuit operation ⁽²⁾⁽⁶⁾
- FAP** Fire alarm panel interface ⁽³⁾⁽⁵⁾⁽⁶⁾
- FM** Flasher module ⁽¹⁾⁽⁵⁾
- AF** Audible/Flasher module ⁽¹⁾⁽⁵⁾
- DC** Remote DC operation ⁽²⁾⁽⁴⁾⁽⁶⁾
- 24K** 220-240VAC, 60 Hz operation

(1) Available on emergency models only.

(2) For use with AC models only.

(3) Operates with 24-volt AC or DC fire alarm panels.

(4) For emergency illumination of sign from remote 6-24 VDC power sources.


(5) -FAP, -FM, and -AF options may not be specified together.

(6) -DC option may not be specified with -2C or -FAP.

Accessories

- PMLXB** Pendant mounting kit (black)
- PMLXW** Pendant mounting kit (white)
- WGLX** Wire guard (Wall mount)
- WG-MLT** Wire guard (Wall mount)
- WGLXC** Wire guard (Ceiling mount)
- WGLXE** Wire guard (End mount)

Dimensions



Hubbell Lighting, Inc.