



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## D2288INS Diagonal Cutting Pliers, Insulated, High Leverage

*Klein Tools*

|                  |  |
|------------------|--|
| Catalog Number   | D2288INS   |
| Manufacturer     | Klein Tools  |
| Description      | These High-Leverage Insulated Diagonal-Cutting Pliers Are 1000V Rated For Safety On The Job. The Thick, Exceptionally Tough White Inner Layer Coating Is Bonded to The Tool. Integral Thumb Guards Prevent Hand Contact With Conductive Parts. The Bright Orange Handles Make This Tool Comfortable to Use All Day and Easy to Identify In The Field. The Durable, Molded Insulation Meets or Exceeds IEC 60900 and Astm F1505 Standards For Insulated Tools. Cutting Knives Are Induction Hardened For Long Life. |
| Weight per unit  | 0.7000 (lbs/each)  |
| Product Category | Pliers, Wrenches, Saw, Pouches   |

### Features

|                |   |
|----------------|---|
| Handle Length  | 4.9" (12.4 cm)  |
| Jaw Length     | 0.781" (2 cm)   |
| jaw thickness  | 0.46" (1.2 cm)  |
| Jaw Width      | 1.25" (3.2 cm)  |
| knife length   | 0.188 (0.5 cm)MaterialSteelOverall Length4.25 (10.8 cm) |
| Material       | Induction Hardened Steel                                |
| tether capable | No  |

### Material, Color, and Finish

|              |        |
|--------------|--------|
| Handle Color | ORANGE |
|--------------|--------|

### Dimensions and Weight

|                |                 |
|----------------|-----------------|
| Overall Length | 8.24" (20.9 cm) |
|----------------|-----------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | DIAGONAL CUTTING PLIERS, INSULATED, HIGH LEVERAGE  |
| extra long description | KLEIN D228-8-INS 8" Insulated, Diag  |
| Features               | These High-Leverage Insulated Diagonal-Cutting pliers are 1000V rated for safety on the job. The thick, exceptionally tough white inner layer coating is bonded to the tool. Integral thumb guards prevent hand contact with conductive parts. The bright orange handles make this tool comfortable to use all day and easy to identify in the field. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools. Cutting knives are induction hardened for long life. |
| Long Description       | These High-Leverage Insulated Diagonal-Cutting pliers are 1000V rated for safety on the job. The thick, exceptionally tough white inner layer coating is bonded to the tool. Integral thumb guards prevent hand contact with conductive parts. The bright orange handles make this tool comfortable to use all day and easy to identify in the field. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools. Cutting knives are induction hardened for long life. |
| Product Type           | 8" Insulated, Diagonal-Cutters   |
| Special Features       | Flame Retardant and Impact Resistant Handle  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Klein Tools    |
| GTIN                      | 00092644720420 |
| Manufacturers Part Number | D2288INS       |
| UPC                       | 092644720420   |

## Taxonomies, Classifications, and Categories

|                      |                         |
|----------------------|-------------------------|
| Category Description | HAND TOOLS              |
| Type                 | Diagonal Cutting Pliers |

## Packaging

|                 |                 |
|-----------------|-----------------|
| Carton          | 1               |
| Package         | 3               |
| Weight          | 11.2 oz (318 g) |
| Weight Per each | 0.7             |

## Uses, Certifications, and Standards

|               |  |
|---------------|--|
| Application   | ACSR, Screws, Nails and Most Hardened Wire |
| Configuration | Tapered Nose                               |
| standard      | IEC 60900 and ASTM F1505                   |