



# Extra-Wide Jaw

## 8" ADJUSTABLE WRENCH



**SAME  
CAPACITY AS A  
STANDARD 12" WRENCH**

For Professionals... Since 1857®

**KLEIN  
TOOLS®**



Extra-Wide Jaw  
D509-8

# Adjustable Wrenches

- **Standard and metric sizes** marked for faster adjustment.
- Manufactured for superior **strength and durability**.
- **Wide handle** for comfortable use.
- **Unique design minimizes protruding jaw shank** for greater capacity in tight spaces.

## Get More Work Done... Faster and Easier

The Klein Tools Adjustable Wrenches you've come to rely on are now even better! Improved features like an **etched inch/metric measurement scale** and a **non-protruding jaw shank** make these wrenches more efficient, especially in tight spaces. A unique **4-threaded knurl worm gear** helps balance these wrenches for smoother operation and allows the user to apply up to **30% more force**.



D509-8



Cat. No.	UPC + 0-92644	Description	Handle	Length	Capacity	Weight (lbs.)
<b>NEW!</b> D509-8	19003-2	8" extra-wide jaw adjustable wrench	plastic dipped – solid blue	8-1/2" (216 mm)	1-1/2" (38 mm)	0.77

### Other Adjustable Wrenches with Improved Features

D506-4	67501-0	4" standard capacity adjustable wrench	plastic dipped – transparent red	4-5/8" (117 mm)	1/2" (13 mm)	0.13
D507-6	67525-6	6" high capacity adjustable wrench	plastic dipped – transparent red	6-1/2" (165 mm)	15/16" (24 mm)	0.27
D507-8	67528-7	8" high capacity adjustable wrench	plastic dipped – transparent red	8-1/4" (209 mm)	1-1/8" (28 mm)	0.62
D507-10	67531-7	10" high capacity adjustable wrench	plastic dipped – transparent red	10-1/4" (260 mm)	1-5/16" (33 mm)	1.00
D507-12	67534-8	12" high capacity adjustable wrench	plastic dipped – transparent red	12-3/8" (314 mm)	1-1/2" (38 mm)	1.24
507-6	67524-9	6" high capacity adjustable wrench	high-polish chrome	6-3/8" (162 mm)	15/16" (24 mm)	0.25
507-8	67527-0	8" high capacity adjustable wrench	high-polish chrome	8-1/8" (206 mm)	1-1/8" (28 mm)	0.51
507-10	67530-0	10" high capacity adjustable wrench	high-polish chrome	10-1/8" (257 mm)	1-5/16" (33 mm)	0.86
507-12	67533-1	12" high capacity adjustable wrench	high-polish chrome	12-1/4" (311 mm)	1-1/2" (38 mm)	1.32
506-15	67515-7	15" high capacity adjustable wrench	high-polish chrome	15-7/8" (403 mm)	1-11/16" (43 mm)	2.92
500-18	67018-3	18" standard capacity adjustable wrench	high-polish chrome	18-1/4" (463 mm)	2-1/16" (52 mm)	4.67
500-24	67021-3	24" standard capacity adjustable wrench	high-polish chrome	24" (610 mm)	2-1/2" (63 mm)	7.76

**KLEIN  
TOOLS**

See our complete line of Combination, Open End, Socket, Specialty and Ratcheting Box Wrenches

[www.kleintools.com](http://www.kleintools.com)



© 2012 Klein Tools, Inc.  
Lincolnshire, IL 60069-1418  
Printed in U.S.A. 96161

Adjustable Wrenches