



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120
75041-0000, TX Garland
Phone: 214-503-7227
Fax: 214-503-9766



DH326NRK 600A/3P HD Fusible Safety Switch W/Neut 240V Nema *Eaton Corp*

Catalog Number	DH326NRK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 600 A, Nema 3R, Painted Galvanized Steel, Class H, Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 75, 200 HP (3PH @STD, TD)), (1)#2-(1)600 Kcmil and (1)#1/0-(1)750 Kcmil Al
Weight per unit	155.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	600
Material	Galvanized Steel
Poles	Three-pole
Voltage Rating	240V

Dimensions and Weight

Depth	12.84
Height	51.83
Width	23.66

Descriptions

Description	600A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA
extra long description	ETN DH326NRK 600A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 600 A, NEMA 3R, Painted galvanized steel, Class H, Neutral, Three-pole, Four-wire, 240 V, Max Hp: 75, 200 hp (3PH @Std, TD)), (1)#2-(1)600 kcmil and (1)#1/0-(1)750 kcmil Al
Product Type	600A/3P HD FSBL Sfty SW W/Neut 240V N3R

Manufacturer Information

Brand	Eaton
GTIN	00782113207421
Manufacturers Part Number	DH326NRK
UPC	782113207421

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120
75041-0000, TX Garland
Phone: 214-503-7227
Fax: 214-503-9766

Packaging

Carton	1
Weight Per each	155

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed, NEC 230.62 (C) Compliant Barrier