



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DMMB44100 44/100A 1000V Fa Multimeter Fuse

Bussmann Fuses

Catalog Number	DMMB44100
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series DMM-B Fuse, Fast Acting Fuse, Multimeters Only, 0.44 A, Non-Indicating, Ferrule End X Ferrule End, 10 Kaic At 1000 Vac/DC, Standard, 1000 V, 1000 VDC
Weight per unit	0.0200 (lbs/each)
Product Category	Current Limiting

Features

amperage rating	44/100 Amp
connection	Ferrule End X Ferrule End
dimensions	0.4600 IN X 0.4600 IN X 1.5000 IN
interrupt rating	20 kA
Material	Melamine Tube
type of indicators	Non-Indicating
Voltage Rating	1000 Vac, 1000 Vdc

Dimensions and Weight

Size	10.00 mm Diameter X 34.90 mm Length
------	-------------------------------------

Descriptions

Description	44/100A 1000V FA MULTIMETER FUSE
extra long description	EFSE DMM-B-44/100 DMM FUSE - BUSSMA
Long Description	Eaton Bussmann series DMM-B fuse, Fast acting fuse, Multimeters only, 0.44 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 1000 Vac/dc, Standard, 1000 V, 1000 Vdc
Product Type	DMM Fuse - Bussmann
Special Features	Nickel Plated Brass Endcap

Manufacturer Information

Brand	Eaton
GTIN	00051712550550
Manufacturers Part Number	DMM-B-44/100
UPC	051712550550

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE

Availability

Manufacturer Status	Inactive
---------------------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked