



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DNBA2020 Bolt On 20A Duplex

Eaton Corp

Catalog Number	DNBA2020
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Thermal Magnetic Circuit Breakers, 20A, 10 Kaic, Two-Pole, #14-4 Awg, Dnba
Weight per unit	1.0 (lbs/each)
Product Category	Wiring Devices

Features

dimensions	3.5000 IN X 0.4000 IN X 3.2500 IN
interrupt rating	10
media	Yes
Poles	2

Descriptions

Description	BOLT ON 20A DUPLEX
extra long description	ETN DNBA2020 BOLT ON 20A DUPLEX
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker, Thermal magnetic circuit breakers, 20A, 10 kAIC, Two-pole, #14-4 AWG, DNBA
Product Type	Bolt On 20A Duplex

Manufacturer Information

Brand	Eaton
GTIN	00782114304709
Manufacturers Part Number	DNBA2020
UPC	782114304709

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous commercial & industrial devices
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

OtherGeneration - Conventional Energy - Conventional
EnergyMarine Vessels and Equipment - Marine Vessels and
Equipment - OtherGeneration - Renewable Energy - Alternative
EnergyDatacenters - IT Space: CI and Hyper Converged

standard

CSA Certified