



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DTVWH Diva 24VDC 30MA 0-10V SP White Lutron

Catalog Number	DTVWH
Manufacturer	Lutron
Description	Diva Dimmer - Gloss Finish, Fluorescent or Led Dimming With 0-10V Ballasts and Drivers, Single-Pole, 120V/30MA/16A In White
Weight per unit	0.3000 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Paddle Switch
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Switch Type	Paddle Switch
Voltage Rating	24

Material, Color, and Finish

Color	White
Finish	Gloss

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

Descriptions

Description	DIVA 24VDC 30MA 0-10V SP WHITE
extra long description	LUT DTV-WH DIVA 0-10V CLASS 2 WHIT
Features	The Diva 0-10V dimmer switch is a simple solution is designed to match existing design style switches and accessories. Easily turn the lights on and off with a paddle switch, and use the slide control to adjust the lights to the perfect level. The new Diva 0 - 10-Volt dimmer switch is a 0-10 VDC dimmer with 3-way functionality for 3rd party 0-10-Volt fixtures (LED and fluorescent), Power Pack (PP-DV) required. Coordinating wall plate and required Power Pack sold separately.
Long Description	Diva Dimmer - Gloss Finish, Fluorescent or LED Dimming with 0-10V Ballasts and Drivers, Single-pole, 120V/30mA/16A in white
Product Type	Diva 0-10V Class 2 White
Special Features	Controls 0-10 V LED or fluorescent fixture loads, 30 mA max control current. Paddle turns on/off. Slide up to brighten, down to dim. Power pack required.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00027557663458
Manufacturers Part Number	DVTV-WH
UPC	027557663458

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer, single-pole

Packaging

Carton	1
Package	24
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Frequency Rating	50 to 60
Mounting	WALLBOX
Operating Temperature standard	32 to 104 UL, CSA