



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7604 Gateway Blvd
77521-0000, TX Baytown
Phone: 832-514-7819
Fax: 832-514-7820



E103B Multivolt 24HR Supercap Indoor/Outdoor 1CH. 40A DP

Nsi Industries

Catalog Number	E103B
Manufacturer	Nsi Industries
Description	Supercap, 24 H Time Setting Mode, DPST Contact Form, 24 H Time Setting, 120 to 277 V Ac, 40 A (No) @ 120 to 277 V Ac (General Purpose);30 A (No) @ 120 V Ac;20 A (No) @ 208 to 277 V Ac (Ballast);15 A (No) @ 120 V Ac (Tungsten);30 A @ 28 V DC (Resistive);40 A (No) @ 120 to 277 V Ac (Inductive), 20 On/Off Cycles, Plastic Enclosure Material, Screw Connection, -40 °F Operating Temperature, +149 °F Operating Temperature, 5.062 X 3.062 X 8.312 In Size, 2 LB
Weight per unit	2.0 (lbs/each)
Product Category	Electronic Time Switches

Features

action	DPST
Base	Screw
Contact Rating	120-277 VAC
Phase	Single Phase
Poles	2
Timing Range	24 Hour

Descriptions

Description	MULTIVOLT 24HR SUPERCAP INDOOR/OUTDOOR 1CH. 40A DP
extra long description	TORK E103B 24 Hour Digital 1 Channe

Manufacturer Information

GTIN	00786261824110
UPC	786261824110

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	24 Hour Time Switch - 1 Or 2 Channel

Packaging

Carton	1
Weight Per each	2

Uses, Certifications, and Standards

Enclosure	NEMA 3R Plastic Indoor-Outdoor
environmental conditions	-40 to + 149 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
standard	UL917