



Powering Business Worldwide

pe.eaton.com

Corrosion Resistant Push-Pull Operator

E34GDB

UPC:782113702858

Dimensions:

- **Height:** 2.2 IN
- **Length:** 1.9 IN
- **Width:** 1.9 IN

Weight: .25 LB

Notes: Use NEMA 4X 10250T operators where exposed to ultraviolet light

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Corrosion Resistant
- **Illumination:** Non-illuminated
- **Number Of Positions:** Two-position
- **Operating Mode:** Maintained push and pull
- **Size:** 30.5 mm
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** E34

Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked
- FDA 3-A



