



Powering Business Worldwide

pe.eaton.com

Special Purpose Limit Switch

E50NN1SPL

UPC:782113761114

Dimensions:

- **Height:** 6.5 IN
- **Length:** 3 IN
- **Width:** 4.5 IN

Weight:1 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 12 Vac, 1A at 125 Vdc
- **Accessories:** Stainless steel shaft
- **Contact Configuration:** 2NO-2NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Series:** E50 Heavy Duty Plug In
- **Switch Type:** Neutral position 5° travel

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50NN1SPL](#)

Certifications: No Data

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Special Purpose Limit Switch

E50NN1SPL

UPC:782113761114

Dimensions:

- **Height:** 6.5 IN
- **Length:** 3 IN
- **Width:** 4.5 IN

Weight: 1 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 12 Vac, 1A at 125 Vdc
- **Accessories:** Stainless steel shaft
- **Contact Configuration:** 2NO-2NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Series:** E50 Heavy Duty Plug In
- **Switch Type:** Neutral position 5° travel

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50NN1SPL](#)

Certifications: No Data

Product compliance: No Data

