



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E51DT1 Ind Prox Sensor Head Only

Eaton Corp

Catalog Number	E51DT1
Manufacturer	Eaton Corp
Description	Eaton E51 Nema Limit Switch Inductive Proximity Sensor, Inductive Proximity Sensor Head, E51, 0.51 In Range, Top Sensing, Shielded, Standard Frequency
Weight per unit	0.1000 (lbs/each)
Product Category	Sensor Accessories

Features

dimensions	1.3800 IN X 1.5100 IN X 1.5100 IN
Material	Plastic

Dimensions and Weight

Depth	1.51
Height	1.51
Width	1.51

Descriptions

Description	IND PROX SENSOR HEAD ONLY
extra long description	ETN E51DT1 IND PROX SENSOR HEAD ONL
Features	Eaton's E51 limit switch style modular sensors are available in thru-beam, reflex, polarized reflex, diffuse reflective and fiber optic sensing modes to solve a wide variety of sensing applications. Modular, plug-in components are easy to maintain, meaning less downtime and reduced inventory. Choose between 2-wire sensors with AC/DC operation and 4-wire sensors in either AC or DC styles. Connection options include terminal, mini-connector and various lengths of cable. Sensors can be ordered in component fo
Long Description	Eaton E51 NEMA limit switch inductive proximity sensor, Inductive Proximity Sensor Head, E51, 0.51 in range, Top Sensing, Shielded, Standard frequency
Product Type	Ind Prox Sensor Head Only

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113344904
Manufacturers Part Number	E51DT1
UPC	782113344904

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Limit switch inductive proximity sensor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.1

Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
Operating Temperature	-13
standard	UL Listed,CSA Certified