

# Eaton EABC26

Catalog Number: EABC26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover	EABC26
	UPC
	782274247809
Product Length/Depth	Product Height
5.56 in	3.75 in
Product Width	Product Weight
2.78 in	4 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

## Product specifications

### Shape

C

### Trade size

3/4"

### Cover opening diameter

3"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page](#)

### Certification reports

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification \(EAB\)](#)

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification \(EAB\)](#)

### Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

[IF 1472 - EAB Condulet Conduit Outlet Bodies](#)

### Specifications and datasheets

[Eaton Specification Sheet - EABC26](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

# Eaton EABC26

Catalog Number: EABC26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover	EABC26
	<b>UPC</b>
	782274247809
<b>Product Length/Depth</b>	<b>Product Height</b>
5.56 in	3.75 in
<b>Product Width</b>	<b>Product Weight</b>
2.78 in	4 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

## Product specifications

### Shape

C

### Trade size

3/4"

### Cover opening diameter

3"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page](#)

### Certification reports

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification \(EAB\)](#)

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification \(EAB\)](#)

### Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

[IF 1472 - EAB Condulet Conduit Outlet Bodies](#)

### Specifications and datasheets

[Eaton Specification Sheet - EABC26](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)