

Eaton EABC26

Catalog Number: EABC26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover	EABC26
	UPC
	782274247809
Product Length/Depth	Product Height
5.56 in	3.75 in
Product Width	Product Weight
2.78 in	4 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

7

9

Product specifications

Shape

C

Trade size

3/4"

Cover opening diameter

3"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page](#)

Certification reports

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification \(EAB\)](#)

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification \(EAB\)](#)

Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

[IF 1472 - EAB Condulet Conduit Outlet Bodies](#)

Specifications and datasheets

[Eaton Specification Sheet - EABC26](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)