

Specifications

Photo is representative

Eaton ECP122408

Eaton Crouse-Hinds series ECP enclosure,
Square cover, 8-15/16" depth, 12" x 24" x 8",
Copper-free aluminum, Tap-in mounting feet

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP122408
UPC	662276322066
PRODUCT LENGTH/DEPTH	17.25 in
PRODUCT HEIGHT	29.25 in
PRODUCT WIDTH	11.63 in
PRODUCT WEIGHT	164 lb



Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 3R 4 7 9

Product specifications

ENCLOSURE SIZE	12" x 24" x 8"
COVER TYPE	Square
DEPTH	8-15/16 in
MATERIAL	Copper-free aluminum
SPECIAL FEATURES	Tap-in mounting feet

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds ECP122408 3D drawing
BROCHURES	Crouse-Hinds series ECP Enclosures Brochure
CATALOGS	Crouse-Hinds series ECP catalog page
CERTIFICATION REPORTS	ECP Explosionproof Enclosures UL certification Intertek EC-Type Examination Certificate IECEX Certificate of Conformity
INSTALLATION INSTRUCTIONS	IF 1107 - Mounting Plate Kit IF 1639 - ECP Explosionproof Enclosures
SPECIFICATIONS AND DATASHEETS	ECP Enclosures Eaton Specification Sheet - ECP122408

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
[Eaton.com](#)

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton ECP122408

Eaton Crouse-Hinds series ECP enclosure,
Square cover, 8-15/16" depth, 12" x 24" x 8",
Copper-free aluminum, Tap-in mounting feet

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP122408
UPC	662276322066
PRODUCT LENGTH/DEPTH	17.25 in
PRODUCT HEIGHT	29.25 in
PRODUCT WIDTH	11.63 in
PRODUCT WEIGHT	164 lb



Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 3R 4 7 9

Product specifications

ENCLOSURE SIZE	12" x 24" x 8"
COVER TYPE	Square
DEPTH	8-15/16 in
MATERIAL	Copper-free aluminum
SPECIAL FEATURES	Tap-in mounting feet

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds ECP122408 3D drawing
BROCHURES	Crouse-Hinds series ECP Enclosures Brochure
CATALOGS	Crouse-Hinds series ECP catalog page
CERTIFICATION REPORTS	ECP Explosionproof Enclosures UL certification Intertek EC-Type Examination Certificate IECEX Certificate of Conformity
INSTALLATION INSTRUCTIONS	IF 1107 - Mounting Plate Kit IF 1639 - ECP Explosionproof Enclosures
SPECIFICATIONS AND DATASHEETS	ECP Enclosures Eaton Specification Sheet - ECP122408

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
[Eaton.com](#)

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

