



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ECS98Z2CAKC1P7S3 Combo BRKR 400A 242A Nema 3R S611 480vac *Eaton Corp*

Catalog Number	ECS98Z2CAKC1P7S3
Manufacturer	Eaton Corp
Description	Eaton S611 Soft Starter, Nema 3R, Disconnect Fuse, Start/Stop, Hand-Off-Auto Selector Switch, 400A Breaker, 242A, 460V
Weight per unit	250.0 (lbs/each)
Product Category	Soft Start Controllers & Start

Features

Coil Voltage	120V/60 Hz
dimensions	61.7500 IN X 28.0000 IN X 10.6800 IN
media	Yes
Voltage Rating	460 V

Dimensions and Weight

Depth	61.75
Height	10.68
Size	242A max RVSS
Width	28

Descriptions

Description	COMBO BRKR 400A 242A NEMA 3R S611 480VAC
extra long description	ETN ECS98Z2CAK-C1P7S3 COM BKR 400A
Features	The Eaton S611 is an innovative, economical soft starter combining advanced functionality, unsurpassed configuration flexibility, and an extremely comprehensive user interface. It is available in both open and enclosed control configurations to meet the needs of the commercial construction and OEM segment.
Long Description	Eaton S611 soft starter, NEMA 3R, disconnect fuse, START/STOP, HAND-OFF-AUTO selector switch, 400A breaker, 242A, 460V
Product Type	Com BKR 400A 242A N3R S611 480V
Special Features	Standard size control power transformer

Manufacturer Information

Brand	Eaton
GTIN	00786685620756
Manufacturers Part Number	ECS98Z2CAK-C1P7S3
UPC	786685620756

Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Soft starter



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	250

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	cUL Listed,UL Listed