



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EGC50 1/2" Emt to 1/2" Flex (Screw In) D/C Coupling *Appleton/Oz Gedney*

Catalog Number	EGC50
Manufacturer	Appleton/Oz Gedney
Description	Emt Fittings, Combination Couplings, Screw-In Compression, Material: Zinc Diecast, UL Standard: 514B, Trade Size: 1/2 - 1/2, Dimension: Length 1.66 Inches, Height 1.00 Inches, Hole Diameter .71, Hole Diameter .72 Inches
Weight per unit	0.0800 (lbs/each)
Product Category	Die Cast Compression Emt to FL

### Features

Connector Type	Compression
insulation	Non Insulated
Material	Zinc Die Cast

### Material, Color, and Finish

Color	Metallic
Finish	Natural

### Dimensions and Weight

Size	0.5
------	-----

### Descriptions

Description	1/2" EMT TO 1/2" FLEX (SCREW IN) D/C COUPLING
extra long description	EGS EGC-50 1/2 EMT - 1/2 FLEX COMB
Long Description	EMT Fittings, Combination Couplings, Screw-in Compression, Material: Zinc diecast, UL Standard: 514B, Trade Size: 1/2 - 1/2, Dimension: Length 1.66 Inches, Height 1.00 Inches, Hole Diameter .71, Hole Diameter .72 Inches
Product Type	1/2 Emt - 1/2 Flex Comb CPLG Comp/SS
Special Features	Combination Coupling 1/2 IN Flex Metal Conduit to EMT Conduit, Screw-In Compression

### Manufacturer Information

Brand	Appleton
GTIN	00687855233854
Manufacturers Part Number	EGC-50
UPC	687855233854

### Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	Combination Coupling EMT TO Flex

### Trade Size

Trade Size	0.5
------------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	25
Package	250
Weight Per each	0.08

## Uses, Certifications, and Standards

Application	Provides a transition from EMT to flexible metal conduit
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E32539, CSA Standard: C22.2 No. 18.3, CSA Certified: 208044; NEMA: FB-1