



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82
76240-0000, TX Gainesville
Phone: 940-612-1388
Fax: 940-612-1499



EGC50 1/2" Emt to 1/2" Flex (Screw In) D/C Coupling *Appleton/Oz Gedney*

Catalog Number	EGC50
Manufacturer	Appleton/Oz Gedney
Description	Emt Fittings, Combination Couplings, Screw-In Compression, Material: Zinc Diecast, UL Standard: 514B, Trade Size: 1/2 - 1/2, Dimension: Length 1.66 Inches, Height 1.00 Inches, Hole Diameter .71, Hole Diameter .72 Inches
Weight per unit	0.0800 (lbs/each)
Product Category	Die Cast Compression Emt to FL

Features

Connector Type	Compression
insulation	Non Insulated
Material	Zinc Die Cast

Material, Color, and Finish

Color	Metallic
Finish	Natural

Dimensions and Weight

Size	0.5
------	-----

Descriptions

Description	1/2" EMT TO 1/2" FLEX (SCREW IN) D/C COUPLING
extra long description	EGS EGC-50 1/2 EMT - 1/2 FLEX COMB
Long Description	EMT Fittings, Combination Couplings, Screw-in Compression, Material: Zinc diecast, UL Standard: 514B, Trade Size: 1/2 - 1/2, Dimension: Length 1.66 Inches, Height 1.00 Inches, Hole Diameter .71, Hole Diameter .72 Inches
Product Type	1/2 Emt - 1/2 Flex Comb CPLG Comp/SS
Special Features	Combination Coupling 1/2 IN Flex Metal Conduit to EMT Conduit, Screw-In Compression

Manufacturer Information

Brand	Appleton
GTIN	00687855233854
Manufacturers Part Number	EGC-50
UPC	687855233854

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	Combination Coupling EMT TO Flex

Trade Size

Trade Size	0.5
------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1725 East Highway 82
76240-0000, TX Gainesville
Phone: 940-612-1388
Fax: 940-612-1499

Packaging

Carton	25
Package	250
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Provides a transition from EMT to flexible metal conduit
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E32539, CSA Standard: C22.2 No. 18.3, CSA Certified: 208044; NEMA: FB-1