



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EHD3070L Type Ehd BRKR 3P 70A 480VAC Max 14kaic

Eaton Corp

Catalog Number	EHD3070L
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, Ehd, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 70A, 18 Kaic At 240 Vac, 14 Kaic At 480 Vac, Line and Load, 50/60 HZ
Weight per unit	4.6 (lbs/each)
Product Category	3 Pole

Features

Current Rating	70A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic

Descriptions

Description	TYPE EHD BRKR 3P 70A 480VAC MAX 14KAIC
extra long description	ETN EHD3070L TYPE EHD BRK 3P 70A 48
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, EHD, Complete breaker, Fixed thermal, fixed magnetic trip type, Three-pole, 70A, 18 kAIC at 240 Vac, 14 kAIC at 480 Vac, Line and load, 50/60 Hz
Product Type	Type Ehd BRK 3P 70A 480VAC Max 14kaic

Manufacturer Information

Brand	Eaton
GTIN	00786679317181
Manufacturers Part Number	EHD3070L
UPC	786679317181

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.55

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
Frequency Rating	50/60 Hz
standard	UL Listed