



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EM3583 1/4 HP 1075 RPM 3 SPD 115V Blower MTR Shaft 1/2"X4

Precision Electric Motor

| | |
|------------------|---|
| Catalog Number | EM3583 |
| Manufacturer | Precision Electric Motor |
| Description | 60 Hertz Frequency Rating; Ul, Csa Approval; Direct Drive Fan and Blower Application; 115 Volt Ac 1-Phase Voltage Rating; Resilient Ring, Extended Stud Mounting; 5 Kilogram Weight; 1/4 HP Power Rating; 1075 RPM Speed Rating; Oao Enclosure Type; Rolled Steel Frame Material; B Insulation Class; 4.2/2.4/2 Amp Motor Fla; Yes Reversible; 3 Speed(S); 1 Service Factor; 48 Nema Frame Size; Economaster[R] Brand; Type Induction Run, Permanent Split Capacitor; Shaft Type Flat; Orientation Horizontal; Bearing Type Bal |
| Weight per unit | 11.0 (lbs/each) |
| Product Category | 20190723150420 |

Descriptions

| | |
|------------------|---|
| Description | 1/4 HP 1075 RPM 3 SPD 115V BLOWER MTR SHAFT 1/2"X4 |
| Long Description | 60 HERTZ FREQUENCY RATING; UL, CSA APPROVAL; DIRECT DRIVE FAN AND BLOWER APPLICATION; 115 VOLT AC 1-PHASE VOLTAGE RATING; RESILIENT RING, EXTENDED STUD MOUNTING; 5 KILOGRAM WEIGHT; 1/4 HP POWER RATING; 1075 RPM SPEED RATING; OAO ENCLOSURE TYPE; ROLLED STEEL FRAME MATERIAL; B INSULATION CLASS; 4.2/2.4/2 AMP MOTOR FLA; YES REVERSIBLE; 3 SPEED(S); 1 SERVICE FACTOR; 48 NEMA FRAME SIZE; ECONOMASTER[R] BRAND; TYPE INDUCTION RUN, PERMANENT SPLIT CAPACITOR; SHAFT TYPE FLAT; ORIENTATION HORIZONTAL; BEARING TYPE BAL |
| Product Type | Unit Bearing Motor |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | |
| GTIN | 00786674019462 |
| Manufacturers Part Number | EC9W115V834 |
| UPC | 786674019462 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Generic HAVCR Motors |
|----------------------|----------------------|

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 11 |