Electronic Voltage Testers

Designed by Electricians for Electricians



 Measures AC and DC voltage at nine common levels up to 600V.

 Bright LEDs indicate voltage reading without batteries installed.

Probe wires with built-in wear indicators.

ET 100 • ET 200



ET200



ELECTRICAL TESTERS

ELECTRICAL TESTERS

Electronic Voltage Testers

MEASUREMENT	ET100, ET200
CAT Rating	CAT IV 600V
Listing	C C USTED US LISTED
Batteries	3 x AAA
Dimensions: 7.375" H x 2.375" W x 1.25" D (187 mm H x 60.3 mm W x 31.8 mm D)	
Weight: 8.1 oz. (230 g)	
ET100 UPC: 0-9264469300-7 ET200 UPC: 0-9264469301-4	

Features for Cat. Nos. ET100 & ET200

- Measures AC and DC voltage at nine common levels up to 600V.
- Bright LEDs indicate voltage reading without batteries installed.
- Low impedance input reduces possibility of ghost voltages.
- Permanently secured test leads are always there when they are needed.
- Molded lead holders are perfect for easy measurements of tamper-proof outlets.
- Vibration and sound alerts for dangerous voltage levels.
- Modern solid-state construction provides CAT IV 600V safety rating.

Additional Features for Cat. No. ET200

- Bright light illuminates work area.
- Audible continuity alerts at less than 270k Ω .

Accessories Available:

Carrying case



Pictured ET200

Standards:

UL 61010-1 2nd edition UL 61010-31 2nd edition CAN/CSA C22.2 No. 61010-01 CAN/CSA C22.2 No. 61010-031



Measure Tamper-Resistant Outlets

120 48 24 12





Work Light

Bright Red LEDs Indicate Voltage Check Circuit Breaker Continuity

AWARNING: Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.









