



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EV1010FBQ 12-10AWG #10STD Ylw Fork TRML *Panduit Corporation*

Catalog Number	EV1010FBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV10-10FB-Q Contractor Grade Vinyl Insulated Fork Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. Accommodates 12-10 Awg Wire Gauge, Compatible With #10 Stud, Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel
media	Yes

Descriptions

Description	12-10AWG #10STD YLW FORK TRML
extra long description	PAN EV10-10FB-Q StrongHold™ EV10-10
Long Description	StrongHold EV10-10FB-Q Contractor Grade Vinyl Insulated Fork Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. Accommodates 12-10 AWG wire gauge, compatible with #10 Stud, are yellow in color, and come in packages of 25.
Product Type	Stronghold™ EV10-10FB-Q Loose Piece Forks, Yellow, Vinyl, 1/

Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983280209
Manufacturers Part Number	EV10-10FB-Q
UPC	074983280209

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
----------------------	-----------

Packaging

Carton	25
Package	250
Weight Per each	0.05