



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EV106FBQ 12-10AWG #6STD Ylw Ring TRML

Panduit Corporation

Catalog Number	EV106FBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV10-6FB-Q Contractor Grade Insulated Fork Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Fork Design Provides For Fast and Easy Installation, Without The Need to Remove Fastener. Accommodates 12-10 Awg, Compatible With #6 Stud (M3.5), Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.1200 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel
media	Yes

Descriptions

Description	12-10AWG #6STD YLW RING TRML
extra long description	PAN EV10-6FB-Q StrongHold™ EV10-6FB
Long Description	StrongHold EV10-6FB-Q Contractor Grade Insulated Fork Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The fork design provides for fast and easy installation, without the need to remove fastener. Accommodates 12-10 AWG, compatible with #6 Stud (M3.5), are yellow in color, and come in packages of 25.
Product Type	Stronghold™ EV10-6FB-Q Loose Piece Forks, Yellow, Vinyl, 1/8

Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983280186
Manufacturers Part Number	EV10-6FB-Q
UPC	074983280186

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
----------------------	-----------

Packaging

Carton	25
Package	250
Weight Per each	0.12