



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EV1410FBQ 16-14AWG #10STD Blue Fork TRML *Panduit Corporation*

Catalog Number	EV1410FBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV14-10FB-Q Contractor Grade Insulated Fork Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Fork Design Provides For Fast and Easy Installation, Without The Need to Remove Fastener. Accommodates 16-14 Awg, Compatible With #10 Stud (M5), Are Blue In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel
media	Yes

Descriptions

Description	16-14AWG #10STD BLUE FORK TRML
extra long description	PAN EV14-10FB-Q StrongHold™ EV14-10
Long Description	StrongHold EV14-10FB-Q Contractor Grade Insulated Fork Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The fork design provides for fast and easy installation, without the need to remove fastener. Accommodates 16-14 AWG, compatible with #10 Stud (M5), are blue in color, and come in packages of 25.
Product Type	Stronghold™ EV14-10FB-Q Loose Piece Forks, Blue, Vinyl, 1/5"

Manufacturer Information

Brand	Panduit®
GTIN	00613056366435
Manufacturers Part Number	EV14-10FB-Q
UPC	613056366435

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
----------------------	-----------

Packaging

Carton	25
Package	250
Weight Per each	0.05