



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EV1410RBQ 16-14AWG #10STD Blue Ring TRML

Panduit Corporation

Catalog Number	EV1410RBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV14-10RB-Q Contractor Grade Insulated Ring Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Ring Tongue Design Assures A Secure Connection In High Vibration Applications. Accommodates 16-14 Awg, Compatible With #10 Stud (M5), Are Blue In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

media	Yes
Voltage Rating	600

Descriptions

Description	16-14AWG #10STD BLUE RING TRML
extra long description	PAN EV14-10RB-Q StrongHold™ EV14-10
Long Description	StrongHold EV14-10RB-Q Contractor Grade Insulated Ring Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The ring tongue design assures a secure connection in high vibration applications. Accommodates 16-14 AWG, compatible with #10 Stud (M5), are blue in color, and come in packages of 25.
Product Type	Stronghold™ EV14-10RB-Q Ring Terminal, Blue, Vinyl, 1/5" Stu

Manufacturer Information

Brand	Panduit®
GTIN	00613056367326
Manufacturers Part Number	EV14-10RB-Q
UPC	613056367326

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
----------------------	-----------

Packaging

Carton	25
Package	250
Weight Per each	0.05