



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F15T8D 15W T8 18" Daylight 62 Cri Bi-Pin Fluor Lamp

Sylvania-Ledvance

Catalog Number	F15T8D
Manufacturer	Sylvania-Ledvance
Description	15W T8 Preheat Fluorescent Lamp, Daylight Phosphor, 6500K Color Temperature, 72 Cri. 7500 Avg Rated Life At 3 HRS/Start
Weight per unit	0.1900 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	7500
Base	Medium Bipin
bulb type	T8
Lamp Type	PREHEAT
lumens	700
Shape	T8
start type	PREHEAT
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	15

Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	15W T8 18" DAYLIGHT 62 CRI BI-PIN FLUOR LAMP
extra long description	SYL F15T8D/21600 F15T8D 24/CS 1/SKU
Long Description	15W T8 preheat fluorescent lamp, Daylight phosphor, 6500K color temperature, 72 CRI. 7500 Avg rated life at 3 hrs/start
Product Type	F15T8D 24/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135216008
Manufacturers Part Number	F15T8/D/21600
UPC	046135216008



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	24
Weight Per each	0.19

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------