



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F32T8SPX41ECOCVG 32W T8 Coated 48" 4100K Med Bi-Pin Fluor Lamp

Ge By Current Lamps

| | |
|------------------|--|
| Catalog Number | F32T8SPX41ECOCVG |
| Manufacturer | Ge By Current Lamps |
| Description | Ge Covrguard®, 32 WTT, 2860 LM, 4100 KV, 85 Cri, 1 In Diameter, 47.78 In Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life |
| Weight per unit | 0.4400 (lbs/each) |
| Product Category | Shatter Resistant Fluorescent |

Features

| | |
|--------------|---------------------|
| average life | 30000.0 |
| Base | Medium Bi-Pin (G13) |
| lumens | 2860.0 |
| Wattage | 32.0 |

Material, Color, and Finish

| | |
|-----------------------------|--------|
| color rendering index (cri) | 85.0 |
| color temperature | 4100.0 |

Dimensions and Weight

| | |
|----------|-------|
| Diameter | 1.0 |
| Length | 47.78 |

Descriptions

| | |
|------------------------|--|
| Description | 32W T8 COATED 48" 4100K MED BI-PIN FLUOR LAMP |
| extra long description | GEL F32T8SPX41ECOCVG 41127 SLIM LIN |
| Long Description | GE covRguard®, 32 WTT, 2860 LM, 4100 KV, 85 CRI, 1 IN Diameter, 47.78 IN Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life |
| Product Type | 41127 Slim Line / F20 |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168411271 |
| Manufacturers Part Number | F32T8SPX41ECOCVG |
| UPC | 043168411271 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | Fluorescent |
|----------------------|-------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 36 |
| Weight Per each | 0.44 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application Shatter-Resistant