



GE  
Lighting

**68922 - F32T8/SPX41/U6/2**

F32T8/SPX41/U6/2



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - U-Shaped
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	20000.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	90.0 mg
Picograms of Mercury (NOM)	1711.027 pg
Primary Application	Full Wattage

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	2800.0
Mean Lumens (NOM)	2630.0
Nominal Initial Lumens per Watt (NOM)	87.5
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	82.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	32.0
---------------	------

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	22.500 in(571.5 mm)
Nominal Length (NOM)	22.500 in(571.5 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**

Product Code	68922
Description	F32T8/SPX41/U6/2
Standard Package	Case
Standard Package GTIN	10043168689226
Standard Package Quantity	12
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
UPC	043168689229