




GE  
Lighting

**66342 - F32T8/SPX65/ECO2**

F32 T8 6500K Product Line Extension



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	30000.0 h
Rated Life (instant start) @ Time	21000 h @ 3 h
Rated Life (rapid start) @ Time	30000 h @ 12 h
	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	35.69268 pg
Primary Application	Full Wattage

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	2900.0
Mean Lumens (NOM)	2755.0
Nominal Initial Lumens per Watt (NOM)	90.625
Color Temperature (NOM)	6500.0 K
Color Rendering Index (CRI) (NOM)	78.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	32.0
---------------	------

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**


Product Code	66342
Description	F32T8/SPX65/ECO2
Standard Package	Case
Standard Package GTIN	10043168663424
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
UPC	043168663427



GE  
Lighting

**66342 - F32T8/SPX65/ECO2**

F32 T8 6500K Product Line Extension



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	30000.0 h
Rated Life (instant start) @ Time	21000 h @ 3 h
Rated Life (rapid start) @ Time	30000 h @ 12 h
	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	35.69268 pg
Primary Application	Full Wattage

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	2900.0
Mean Lumens (NOM)	2755.0
Nominal Initial Lumens per Watt (NOM)	90.625
Color Temperature (NOM)	6500.0 K
Color Rendering Index (CRI) (NOM)	78.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	32.0
---------------	------

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**

Product Code	66342
Description	F32T8/SPX65/ECO2
Standard Package	Case
Standard Package GTIN	10043168663424
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
UPC	043168663427